





REV.	REVISION DESCRIPTION	DATE	APPD



NOTES:

Rated voltage: 50V AC/DC

Rated current: 1A AC DC

Contact resistance: $\leq 20 \text{ m}\Omega$

Insulation resistance: $\geq 100 \text{ M}\Omega$


Withstand voltage: 250V AC/minute

Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$


Wire range: AWG#28~#26

Materials:


Terminal: Phosphor bronze, Tin plated



SECTION A-A



SECTION B-B



SECTION C-C

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL37002(3701)-T	TITLE: 3.7mm Pitch Crimp Terminal
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 20.10.13
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 20.10.13
FINISH:		APPD: Ren An De	DATE: 20.10.13
DRAWING NO:		UNITS: mm	PAGE: 1/1
		REV.: A	