

博穆电子有限公司

BOMU ELECTRONICS CO., LTD

VH 条形连接器 (3.96mm)

技术参数 TECHNICAL PARAMETER

间距(PITCH):3.96mm

极数(Poles):2--16

适用基板厚度(Applicable PC board thickness):1.6mm

额定电流(Current rating):5A,AC,DC

额定电压(Voltage rating):250V,AC,DC

工作温度(Working Temperature):-25℃~+85℃

耐压值(Withstand voltage):1500V,AC/min

接触电阻(Contact resistance):≤0.01 Ω

绝缘电阻(Insulation resistance):≥1000M Ω

没有标注公差± 0.2


材料 MATERIAL

基座(HOUSING):尼龙66UL94V-0(NYLON66 UL94V-0)
插针(PIN):黄铜(BRASS)表面镀纯锡(PURE TIN-PLATED)



极数 Poles	编号 Part Number	尺寸 Dimensions/mm	
		A	B
2	VH-2Y	VH-2A(W/T)	3.96 7.92
3	VH-3Y	VH-3A(W/T)	7.92 11.88
4	VH-4Y	VH-4A(W/T)	11.88 15.84
5	VH-5Y	VH-5A(W/T)	15.84 19.80
6	VH-6Y	VH-6A(W/T)	19.80 23.76
7	VH-7Y	VH-7A(W/T)	23.76 27.72
8	VH-8Y	VH-8A(W/T)	27.72 31.68
9	VH-9Y	VH-9A(W/T)	31.68 35.64
10	VH-10Y	VH-10A(W/T)	35.64 39.60
11	VH-11Y	VH-11A(W/T)	39.60 43.56
12	VH-12Y	VH-12A(W/T)	43.56 47.52
13	VH-13Y	VH-13A(W/T)	47.52 51.48
14	VH-14Y	VH-14A(W/T)	51.48 55.44
15	VH-15Y	VH-15A(W/T)	55.44 59.40
16	VH-16Y	VH-16A(W/T)	59.40 63.36

端子 (TERMINAL)

VH-nT





阴连接器 (HOUSING)
VH-nY





阳连接器(直式) (WAFER-180°)

VH-nA



阳连接器(弯式) (WAFER-90°)

VH-nAW



阳连接器(长弯式) (LONG WAFER-90°)

VH-nAWT

