

1 2 3 4 5 6 7 8

Dept

Qty

DC 1

ED 1

FE 1

ISO 1

PD 1

R&D 1

SD 1

QA 1

QC 1

QE 1

晨翔2.54mm TJC8 TYPE 黑色2*22pin胶芯

晨翔料号: I-DS1071-SCB02x22

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	WPY 11/09/24'		

1. 电性说明:

- 1.1 耐压: 500伏交流电一分钟
- 1.2 绝缘阻抗: 1000兆欧最小
- 1.3 额定电流: 3安

2. 环境特性:

- 2.1 工作温度: -25~+85° C

3. 材料:

- 3.1 胶芯: PA66, 黑色

55.88

53.34

2.54

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	
X.	±0.60	X.	±5°	UNITS	mm	2.54mm TJC8 TYPE 黑色2*22pin胶芯	
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1071 SERIES
.XX	±0.25	.XX	±2°	晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD			
DRAWING TYPE		CUSTOMER					
SCALE		1:1	SHEET 1 OF 1				
DRAWING NO.		C-DS1071-XXXXX-A					

1 2 3 4 5 6 7 8