








RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM



PCB.WELDING DRAWING

Specification

Operating Life	100,000
Contact rating	50mA@12V DC.
Insulation resistance	100 MΩ min.
Contact resistance	100mΩ max.initial.
Dielectric Strength	250 V AC(1mn)
Travel	0.2±0.1mm
Storage Temperature	- 30°C to 105°C

Mechanical

ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/CO LOR
E	Button	PPA	1	Black
D	COVER	Brass	1	Cleaning
C	DOME	Stainless Steel	1	Plated Ag
B	HOUSING	PPA	1	Black
A	PIN	PHOSPHOR BRONZE	1	Plated Ag

Type	Operating Force(gf)	Height mm	Button	Leads Shape(G, J, T)	Ground pin (0,1)	Pegs Option(0,1)
YTS1R001	2	250±50	U 22 T 16 S 9.5 R 4.5 Q 15.0 P 13.0 O 12.0 N 11.0 M 10.5 L 10.0 K 9.0 J 8.5 H 8.0 G 7.5 F 7.0 E 6.5 D 6.0 C 5.5 B 5.0 A 4.3	B (BLACK) T	0 (None)	0 (None)
	1	160±50				

X. ±0.50	X.° ±2°	UNITS mm
.X ±0.30	.X° ± 1°	MAT'L
.XX ±0.10	.XX° ± 0.5°	FINISH
.XXX ± 0.05		Q'TY

YIYUAN TECHNOLOGY	
SERIES NO. YTS1R001	TITLE: TACTILE SWITCH 6x6插脚
APPD: ROGER	DWG NO.: YTS1R001
CHKD: ROC	
DR: BILLY WANG 2020/08/21	

Packaging:
1000 pieces Bulk

SCALE	SHEET	REV.
1/1	1/1	A1