

1 2 3 4 5 6 7 8

Dept Qty 晨翔2.54mm TJC8 TYPE 黑色1*25pin胶芯

DC 1

ED 1

FE 1 晨翔料号: I-DS1071-SCB01x25

ISO 1

PD 1

R&D 1

SD 1

QA 1

QC 1

QE 1

1. 电性说明:

1.1 耐压: 500伏交流电一分钟

1.2 绝缘阻抗: 1000兆欧最小

1.3 额定电流: 3安

2. 环境特性:

2.1 工作温度: -25~+85° C

3. 材料:

3.1 胶芯: PA66, 黑色

2.54

63.50

60.96

2.54

14.00

2.54

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	
X.	±0.60	X.	±5°	mm		2.54mm TJC8 TYPE 黑色1*25pin胶芯	
.X	±0.38	.X	±3°	A4		SERIES DS1071 SERIES	
.XX	±0.25	.XX	±2°				

DRAWING TYPE CUSTOMER

SCALE 1:1 SHEET 1 OF 1

DRAWING NO. C-DS1071-XXXXX-A

晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD