

1 2 3 4 5 6 7 8

Dept Qty 晨翔2.54mm TJC8 TYPE 黑色1*40pin胶芯

DC 1

ED 1

FE 1 晨翔料号: I-DS1071-SCB01x40

ISO 1

PD 1

R&D 1

SD 1

QA 1

QC 1

QE 1

1. 电性说明:

1.1 耐压: 500伏交流电一分钟

1.2 绝缘阻抗: 1000兆欧最小

1.3 额定电流: 3安

2. 环境特性:

2.1 工作温度: -25~+85° C

3. 材料:

3.1 胶芯: PA66, 黑色

2.54

101.60

99.06

2.54

14.00

2.54

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE
X.	±0.60	X.	±5°	mm	2.54mm TJC8 TYPE 黑色1*40pin胶芯
.X	±0.38	.X	±3°		
.XX	±0.25	.XX	±2°		

DRAWING TYPE		CUSTOMER	
SCALE	1:1	SHEET	1 OF 1
DRAWING NO.	C-DS1071-XXXXX-A		

晨翔电子有限公司

CONNPLY CONNPLY ELECTRONIC CO. LTD

2.54mm TJC8 TYPE 黑色1*40pin胶芯

DS1071 SERIES

1 2 3 4 5 6 7 8