





1		2		3		4		5		6					
A	芯位排布			技术参数	芯数	2	3	4	4D	5	5B	6	8	12	17
					额定电流/电压	4A/250V	4A/250V	4A/250V	4A/250V	4A/60V	4A/60V	2A/30V	2A/30V	1.5A/30V	1.5A/30V
					额定脉冲电压	2500V	2500V	2500V	2500V	1500V	1500V	800V	800V	800V	800V
					绝缘电阻 (MΩ)	≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100
					接触电阻 (mΩ)	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5
B	面板开孔尺寸														
				A: 焊杯高度 											
D	6	焊线式母针直针镀金	pc	2~17	GENERAL TOLERANCE (UNLESS SPECIFIED)	绘图 DWN	W. M 2024. 8. 24								
	5	六角螺母黄铜 M12*1螺纹, (M12座子螺母) 亮镍	pc	1											
	4	丁腈橡胶 φ12*φ8*2黑色	pc	1	确认 CHK	品名 TITLE						M12板前安装孔型金属插座 焊线式 锁板牙M12*1			
	3	M12螺纹式板前, 母座铜外壳 锁板牙M12*1	pc	1										核准 APVD	
	2	M12 孔型胶芯短体带倒角 黑色	pc	1	单位 UNIT	MM	版本 REV	A	品号 PART NO						
	1	丁腈橡胶 φ9*φ6*1.5黑色	pc	1											
No.		Specification	Unit	Q'ty	 视 角 THIRD ANGLE	尺寸 SIZE	A4	页码 SHEET	1 OF 1	型号 DRAWING NO		M12-Sxx-GWBM12			
1		2	3		4		5		6						