




1		2		3		4		5		6											
芯位排布										芯数	2	3	4	4D	5	5B	6	8	12	17	
										额定电流/电压	4A/250V	4A/250V	4A/250V	4A/250V	4A/60V	4A/60V	2A/30V	2A/30V	1.5A/30V	1.5A/30V	
										额定脉冲电压	2500V	2500V	2500V	2500V	1500V	1500V	800V	800V	800V	800V	
										绝缘电阻 (MΩ)	≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100	
										接触电阻 (mΩ)	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5	≤ 5	



技术参数				GENERAL TOLERANCE (UNLESS SPECIFIED)		DWN		DATE					
						W.M		2024.6.20					
						CHK		DATE					
						APVD		DATE		TITLE			
连接方式: 螺纹连接				≤10 ±0.1		UNIT		REV		PART NO			
接线方式: 焊线				<10~≤20 ±0.2		MM		A		DRAWING NO			
污染等级: 3				<20~≤50 ±0.5		SIZE		SHEET		M12-Pxx-PWAP7			
温度范围: -40℃ ~ +80℃				Angle ±1°		A4		1 OF 1					
防护等级: IP67						THIRD ANGLE							
插拔周期: ≥500													
外壳材料: 尼龙, 黑色													
接触体材料: 铜, 镀金													
绝缘体材料: 增强尼龙, 黑色													
密封材料: 橡胶, 黑色													