

	1	2	3	4	5	6	8	12																																																			
P.C.B. 开孔尺寸									技术参数 <table border="1"> <thead> <tr> <th>芯数</th><th>2</th><th>3</th><th>4</th><th>4D</th><th>5</th><th>5B</th><th>6</th><th>8</th><th>12</th></tr> </thead> <tbody> <tr> <td>额定电流/电压</td><td>4A/250V</td><td>4A/250V</td><td>4A/250V</td><td>4A/250V</td><td>4A/60V</td><td>4A/60V</td><td>2A/30V</td><td>2A/30V</td><td>1.5A/30V</td></tr> <tr> <td>额定脉冲电压</td><td>2500V</td><td>2500V</td><td>2500V</td><td>2500V</td><td>1500V</td><td>1500V</td><td>800V</td><td>800V</td><td>800V</td></tr> <tr> <td>绝缘电阻(MΩ)</td><td>≥100</td><td>≥100</td><td>≥100</td><td>≥100</td><td>≥100</td><td>≥100</td><td>≥100</td><td>≥100</td><td>≥100</td></tr> <tr> <td>接触电阻(mΩ)</td><td>≤5</td><td>≤5</td><td>≤5</td><td>≤5</td><td>≤5</td><td>≤5</td><td>≤5</td><td>≤5</td><td>≤5</td></tr> </tbody> </table>	芯数	2	3	4	4D	5	5B	6	8	12	额定电流/电压	4A/250V	4A/250V	4A/250V	4A/250V	4A/60V	4A/60V	2A/30V	2A/30V	1.5A/30V	额定脉冲电压	2500V	2500V	2500V	2500V	1500V	1500V	800V	800V	800V	绝缘电阻(MΩ)	≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100	接触电阻(mΩ)	≤5	≤5	≤5	≤5	≤5	≤5	≤5	≤5	≤5
芯数	2	3	4	4D	5	5B	6	8	12																																																		
额定电流/电压	4A/250V	4A/250V	4A/250V	4A/250V	4A/60V	4A/60V	2A/30V	2A/30V	1.5A/30V																																																		
额定脉冲电压	2500V	2500V	2500V	2500V	1500V	1500V	800V	800V	800V																																																		
绝缘电阻(MΩ)	≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100																																																		
接触电阻(mΩ)	≤5	≤5	≤5	≤5	≤5	≤5	≤5	≤5	≤5																																																		
	B 过板插针孔径尺寸: 2~5P: Ø1mm 8P: Ø0.8mm 12P: Ø0.6mm								技术参数 连接方式: 螺钉连接 接线方式: 焊板 污染等级: 3 温度范围: -40°~+80° 防护等级: IP67 插拔周期: ≥500																																																		
									GENERAL TOLERANCE (UNLESS SPECIFIED) <table border="1"> <tbody> <tr> <td>≤10</td><td>±0.1</td></tr> <tr> <td><10~≤20</td><td>±0.2</td></tr> <tr> <td><20~≤50</td><td>±0.5</td></tr> <tr> <td>Angle</td><td>±1°</td></tr> </tbody> </table> 绘图 DWN W. M 2024. 8. 24 确认 CHK 核准 APVD 品名 TITLE M12弯式孔型金属插座 插板式 锁板牙M12*1 品号 PART NO 型号 DRAWING NO M12-Sxx-GPLM12	≤10	±0.1	<10~≤20	±0.2	<20~≤50	±0.5	Angle	±1°																																										
≤10	±0.1																																																										
<10~≤20	±0.2																																																										
<20~≤50	±0.5																																																										
Angle	±1°																																																										
芯位排布	视角 THIRD ANGLE								单位 UNIT MM 版本 REV A 页码 SHEET 1 OF 1																																																		
D	1	2	3	4	5	6	8	12																																																			

表单编号: QR-21-020 版本 A1