

1		2		3		4		5		6		
芯位排布					芯数		3		4		4D	
					额定电流/电压		3A/60V		3A/60V		4A/60V	
					额定脉冲电压		1500V		1500V		1500V	
					绝缘阻抗 (MΩ)		≥100		≥100		≥100	
					接触阻抗 (MΩ)		≤ 5		≤ 5		≤ 5	
P.C.B开孔尺寸												
技术参数				A: 3~5P: 7.68mm 6P: 6.48mm 8P: 6.15mm B: 3~5P: Ø1mm 6~8P: Ø0.6mm								
连接方式: 螺纹连接												
接线方式: 焊板												
污染等级: 3												
温度范围: -40℃ ~ +80℃												
防护等级: IP67												
插拔周期: ≥500												
8 M8弯式座子母头定位板 S式LCP, 黑色				pc		1		GENERAL TOLERANCE (UNLESS SPECIFIED)				
7 插板式母针弯针镀金				pc		3~8		≤10 ±0.1				
6 M8卡扣式, 90° 屏蔽铜外壳				pc		1		<10~≤20 ±0.2				
5 丁腈橡胶 φ10*φ7*1.5 黑色				pc		1		<20~≤50 ±0.5				
4 六角螺母黄铜 M10*0.75螺纹 (M8弯式板后母座螺母) 亮镍				pc		1		Angle ±1°				
3 M8螺纹式板后, 母座弯式铜外壳 锁板牙M10*0.75				pc		1		绘图 DWN				
2 丁腈橡胶 φ7*φ5.4*0.8 黑色				pc		1		W. M 2024. 8. 26				
1 M8 孔型胶芯长体带倒角 黑色				pc		1		确认 CHK				
No. Specification				Unit		Q'ty		核准 APVD				
								品名 TITLE				
								M8弯式孔型金属插座 插板式 锁板牙M10*0.75				
								品号 PART NO				
								型号 DRAWING NO				
								M8-Sxx-GPLM10				