

芯位排布	1		2		3	4	5	6			
					芯数	3	4	4D	5	6	8
					额定电流/电压	3A/60V	3A/60V	4A/60V	3A/30V	1.5A/30V	1.5A/30V
					额定脉冲电压	1500V	1500V	1500V	800V	800V	800V
					绝缘阻抗 (MΩ)	≥100	≥100	≥100	≥100	≥100	≥100
						接触阻抗 (MΩ)	≤5	≤5	≤5	≤5	≤5
P.C.B开孔尺寸											