







| REV  | DESCRIPTION | DRW  | DATE       |
|------|-------------|------|------------|
| A/01 |             | OUXH | 2020.08.14 |
|      |             |      |            |

# SPECIFICATION:

- 1.RatedCurrent:10mA100mA2VDC30VDC
- 2.Contact Resistance:Initial 50mΩ
- 3.Insulation Resistance:100MΩ Min
- 4.With stand Voltage:500VDC50HzFor1Min
- 5.LifeTest:500,000Cycles
- 6.OperatingForce 5N,Travel:1mm
- 7.OperatingTemperature:-40℃~85℃



## SCHEMATIC



Without permission, copying is strictly prohibited. YIYUAN

中心孔距  
皆为±0.05

一般公差  
0~150 : ±0.05  
>151~300 : ±0.1  
>301~500 : ±0.2  
>501~1000 : ±0.3

|    |          |      |     |    |          |
|----|----------|------|-----|----|----------|
| 製圖 | P.M.D    | 比例   | 5:1 | 日期 | 15/11/20 |
| 設計 | Luo Jie  | 單位   | mm  | 材質 |          |
| 校對 | Roger Li | 全週倒角 |     | 數量 |          |
| 審核 | Roc Zhao | 視圖   |     | 處理 |          |

YIYUAN TECHNOLOGY

|    |               |    |               |
|----|---------------|----|---------------|
| 圖號 | YTSK12-BA1-5N | 機型 | YTSK12 Series |
| 設備 |               | 圖名 |               |