

P. C. B. 开孔尺寸

1 2

3

4

5

6

7


8

9

10


11

12

[illegible]

芯位排布

1 3 2P	1 3 4 3P	1 2 3 4 4P	1 2 3 4 4P D	1 2 3 4 5 5P
1 2 3 4 5 5P B	1 2 3 4 6 7 6P	1 2 3 4 6 7 7P	1 2 3 4 5 6 7 8P	1 2 3 4 5 6 7 8 9 10 11 12 12P
1	2	3		

GENERAL TOLERANCE (UNLESS SPECIFIED)		绘图 DWN		W. M 2024.8.24		 正成	
≤10 ±0.1		确认 CHK				品 名 TITLE M12弯式针型金属插座 插板式 锁板牙M12*1 带屏蔽	
<10~≤20 ±0.2							
<20~≤50 ±0.5		核准 APVD					
Angle ±1°							
 视 角 THIRD ANGLE		单位 UNIT	MM	版本 REV	A	品 号 PART NO	
		尺寸 SIZE	A4	页码 SHEET	1 OF 1	型 号 DRAWING NO	M12-Pxx-GPLM12-JD
4			5			6	