




1		2		3		4		5		6						
芯位排布						芯数		3		4						
						额定电流/电压		3A/60V		3A/60V						
						额定脉冲电压		1500V		1500V						
						绝缘阻抗 (MΩ)		≥100		≥100						
						接触阻抗 (MΩ)		≤ 5		≤ 5						
P.C.B开孔尺寸																
面板开孔尺寸																
																
技术参数																
连接方式:						螺纹连接										
接线方式:						焊板										
污染等级:						3										
温度范围:						-40°C ~ +80°C										
防护等级:						IP67										
插拔周期:						≥500										
4	通孔式公针弯针镀金 OD:1.0				pc	3~4	GENERAL TOLERANCE (UNLESS SPECIFIED)		绘图 DWN		W. M 2024. 8. 26					
3	丁腈橡胶 φ10*φ7.6*1.2黑色				pc	1	≤10 ±0.1 <10~≤20 ±0.2 <20~≤50 ±0.5 Angle ±1°		确认 CHK						品名 TITLE	M8弯式针型塑料插座 通孔式 锁板牙M8*1
2	六角螺母黄铜 M8*1螺纹 (M8板后螺母) 亮镍				pc	1			核准 APVD						品号 PART NO	
1	M8 A编码公插芯,通孔式,黑色				pc	1					单位 UNIT	MM	版本 REV	A	型号 DRAWING NO	M8-PxA-PTLM8
No.	Specification				Unit	Q'ty	视角 THIRD ANGLE		尺寸 SIZE	A4	页码 SHEET	1 OF 1				
1		2		3		4		5		6						