






1		2		3		4		5		6						
芯位排布				技术 参 数		芯数	2	3	4	4D	5	5B	6	8	12	17
		额定电流/电压	4A/250V			4A/250V	4A/250V	4A/250V	4A/60V	4A/60V	2A/30V	2A/30V	1.5A/30V	1.5A/30V		
		额定脉冲电压	2500V			2500V	2500V	2500V	1500V	1500V	800V	800V	800V	800V		
		绝缘电阻 (MΩ)	≥100			≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100	≥100		
		接触电阻 (mΩ)	≤5			≤5	≤5	≤5	≤5	≤5	≤5	≤5	≤5	≤5		
面板开孔尺寸						A: 焊杯高度										
				技术参数												
				连接方式: 螺纹连接												
				接线方式: 焊线												
				污染等级: 3												
				温度范围: -40°~+80°												
				防护等级: IP67												
				插拔周期: ≥500												
6		焊线式母针直针镀金		pc	2~17	GENERAL TOLERANCE (UNLESS SPECIFIED)		绘图 DWN		W. M 2024. 8. 24						
5		六角螺母黄铜 PG9螺纹 (M12座子螺母) 亮镍		pc	1	≤10 ±0.1		确认 CHK								
4		丁腈橡胶 φ16*φ12*2黑色		pc	1	<10~≤20 ±0.2		核准 APVD				品名 TITLE		M12板前安装孔型金属插座 焊线式 锁板牙PG9		
3		M12螺纹式板前, 母座铜外壳 锁板牙PG9		pc	1	<20~≤50 ±0.5						品号 PART NO				
2		M12 孔型胶芯长体带倒角 黑色		pc	1	Angle ±1°				单位 UNIT	MM	版本 REV	A	型号 DRAWING NO		
1		丁腈橡胶 φ9*φ6*1.5黑色		pc	1			视角 THIRD ANGLE		尺寸 SIZE	A4	页码 SHEET	1 OF 1	M12-Sxx-GWBP9		
No.		Specification		Unit	Q'ty											
1		2		3		4		5		6						