

A	1			2			3			4		5		6		
	芯位排布									芯数	3	4	4D	5B	6	8
										额定电流/电压	3A/60V	3A/60V	4A/60V	3A/30V	1.5A/30V	1.5A/30V
										额定脉冲电压	1500V	1500V	1500V	800V	800V	800V
										绝缘阻抗 (MΩ)	≥100	≥100	≥100	≥100	≥100	≥100
									接触阻抗 (MΩ)	≤5	≤5	≤5	≤5	≤5	≤5	
B	P.C.B开孔尺寸															
C	面板开孔尺寸									技术参数 连接方式: 螺纹连接 接线方式: 焊板 污染等级: 3 温度范围: -40°C ~ +80°C 防护等级: IP67 插拔周期: ≥500						
D	5	插板式公针直针镀金			pc	3~8	GENERAL TOLERANCE (UNLESS SPECIFIED)		绘图 DWN		W. M 2024. 8. 26					
	4	六角螺母黄铜 M8*0.5螺纹 (M8板前螺母) 亮镍			pc	1	≤10 ±0.1		确认 CHK							
	3	丁腈橡胶 φ9*φ6*1.5黑色			pc	1	<10~≤20 ±0.2		核准 APVD							
	2	M8螺纹式板前,公座双切边铜外壳 锁板牙M8*0.5			pc	1	<20~≤50 ±0.5						品名 TITLE	M8板前安装针型金属插座 插板式 锁板牙M8*0.5		
	1	M8 针型胶芯短体 黑色			pc	1	Angle ±1°		单位 UNIT		MM	版本 REV	A	品号 PART NO		
	No.	Specification			Unit	Q'ty			尺寸 SIZE		A4	页码 SHEET	1 OF 1	型号 DRAWING NO	M8-Px-GPBM8	
1		2		3		4		5		6						