





NOTES:

MATERIAL

1.HOUSING MATERIAL: LCP BLACK UL94V-0

2.CONTACT MATERIAL: C5191 R-H,T=0.30mm

3.SHELL: BRASS R-H,T=0.2mm

FINISH:

1.CONTACT PLATING: 50u" MIN. NICKEL PLATED UNDER ALLOVER
80u" MIN. TIN PLATED IN SOLDERING AREA

2.SHELL PLATING: 30u" MIN NICKEL PLATED ALLOVER
GOLD PLATED IN CONTACT AREA

ELECTRICAL:

1.VOLTAGE RATING: 125 VAC RMS

2.CURRENT RATING: 1.5 AMP

3.CONTACT RESISTANCE: 30 MILLIOHMS MAX

4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 500V DC

5.DIELECTRIC WITHSTANDING VOLTAGE : 500V AC R.M.S MIN

MECHANICAL:

1.DURRABILITY: 750 CYCLES MIN

2.PCB RETENTION PRE-SOLDER: 1 LB MIN.

序号	名称	材料	表面	备注
3	外壳	黄铜	镀镍	
2	端子	C5191	焊料区镀锡， 接触区镀金(1u)	
1	基座	LCP	黑色	

Ordering Information

HC-RJ45 - *** * - * - * * * - 06

Series (系列号)	Connector Package 形式:MDP S=SMT	Ports 1:1 (1) 2:2 (2)	LED/EMI Style 1:无灯 2:带灯无弹 3:带灯 4:无灯无弹 5:带灯有弹 6:无弹 7:半包	LED Color 1:黄 (左绿右黄) 2:绿 (左绿右绿) 3:蓝 (左绿右蓝) 4:蓝 (左蓝右蓝) 5:带灯有弹 6:带灯 (带灯左绿) 7:带灯 (带灯右绿) 8:带灯 (带灯右蓝)	Type T-卧式 V-立式	产品序号
1012 0106 0109						

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK	产品名称 TITLE	网络插座 (沉板1.1 带灯无弹 DIP 16.18x9.9x14.6 带双耳)	版本 REV.	A
			X.X ±0.30	批准 APPROVAL	产品料号 PART NO.	HC-RJ45-1012-1-2-1M01-06	单位 UNITS	mm
			X.XX ±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10	投影 Projection				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					