









NOTE:

- MATERIAL:
 - HOUSING: THERMOPLASTIC FLAMMABILITY UL94V-0 BLACK
 - CONTACT: COPPER ALLOY (T=0.35mm)
 - SHELL: COPPER ALLOY (T=0.2mm)
- FINISH:
 - CONTACT: Gold plating in contact area, tin plating in welding area.
 - SHELL: NICKEL PLATING OVERALL

ELECTRICAL:

- VOLTAGE RATING: 125 VAC RMS
- CURRENT RATING: 1.5 AMP
- CONTACT RESISTANCE: 30 MILLIOHMS MAX
- INSULATION RESISTANCE: 500 MEGOHMS MIN @ 500V DC
- DIELECTRIC WITHSTANDING VOLTAGE : 500V AC R. M. S MIN

MECHANICAL:

- DURRABILITY: 750 CYCLES MIN
- QTY/REEL: 200PCS

序号	名称	材料	表面	备注
3	外壳	黄铜	镀镍	
2	端子	C5191	焊料区镀锡， 接触区镀金(1u)	
1	底座	LCP	黑色	

Ordering Information

HC-RJ45 - *** * - * - * * * - 06

Series (系列号)	Connector Package 默认=DIP S=SMT	Ports 1:1 (1) 2:2 (2)	LED/EMI Style 1: 有灯无弹 2: 有灯有弹	LED Color 1: 绿灯 (左绿右绿) 2: 蓝灯 (左蓝右蓝) 3: 无灯无弹 4: 无灯有弹 5: 有灯无弹 6: 有灯有弹 7: 全黑 8: 带灯 (带灯右绿)	Type T=卧式 V=立式	产品序号
1012 0106 0109						

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	网络插座 (卧贴 无灯无弹 15.3x10.7x15.3 无柱 带4插脚)		版本 REV.
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	HC-RJ45-0106S-1-4-T01-06		单位 UNITS
			X.XXX ±0.10	投影 Projection	材料 MATERIAL			页次 SHEET
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					1/1
1	初版发行							