




- NOTES:
- 1. MATERIAL:
 - 1.1. HOUSING: LCP ,COLOR IS BLACK;
 - 1.2. CONTACT: PHOSPHOR COPPER(T=0.3MM) ;
 - 1.3. SHELL: SUS (T=0.2mm) ;
 - 2. FINISH: GOLD PLATED G/Fu";
 - 4. ELECTRICAL:
 - 4.1. VOLTAGE RATING: 125 VAC RMS;
 - 4.2. CURRENT RATING: 1.5 AMP;
 - 4.3. CONTACT RESISTANCE: 35MILLIOHMS MAX.;
 - 4.4. WITHSTAND VOLTAGE: 500 VAC RMS 50(60)Hz,1MIN.;
 - 4.5. INSULATION RESISTANCE: 500MEGOHMS MIN @500V DC.;
 - 5. MECHANICAL:
 - 5.1. MATING/UNMATING FORCE: 22N MAX.;
 - 5.2. RETENTION STRENGTH: 50N MIN.;
 - 5.3. OPERATING LIFE: 750 CYCLES MIN.;
 - 6. ENVIRONMENTAL:
 - 6.1. STORAGE TEMPERATURE RANGE: -40℃~+85℃;
 - 6.2. OPERATION TEMPERATURE RANGE: -25℃~+70℃;
 - 7.SALT SPRAY TEST:8H(EXCLUDING RIVETED BENDS)

序号	名称	材料	表面	备注
3	外壳	SUS	镀镍	
2	端子	磷铜	焊料区镀锡， 接触区镀金(1u)	
1	基座	LCP	黑色	

Ordering Information

HC-RJ45 - *** * - * - * * * - 06

Series (系列号)	Connector Package 默认=DIP S=SMT	Ports 1:1 1:2 2: 带灯无弹	LED/EMI Style 1: 带灯 2: 无灯	LED Color 1: 带灯 (左黄右绿) 2: 带灯 (左蓝右绿) 3: 带灯 (左蓝右黄) 4: 无灯无弹 5: 带灯无弹 6: 带灯 (带灯左黄) 7: 带灯 (带灯左蓝) 8: 带灯 (带灯右黄) 9: 带灯 (带灯右蓝)	Type 1: 沉板式 2: 立式	产品序号
1012 0106 0109						

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK	产品名称 TITLE	网络插座 (沉板5.65 带灯无弹 DIP 16.2x9.9x15.4)	版本 REV.	A
			X.X ±0.30	批准 APPROVAL	产品料号 PART NO.	HC-RJ45-0109-1-2-1M03-06	单位 UNITS	mm
			X.XX ±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10	投影 Projection				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					
1	初版发行							