



备注

紫铜T2, 镍底, 镀雾锡

压线螺孔M6

额定电流: 100A

工作温度: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$

pin deformation and burrs.

不得有脚变形,毛刺等缺陷

未标注的尺寸参考公差

HC - * * * * - ***** - D *** * - 02

Type	Screw Thread	Welding Twist	T=Anti Twist	Series	D=DIP	Product No.	Material
M-Pull Teeth (抽牙)	3-M3 (螺牙)	(焊脚)	(防止扭动)	0808-8x8mm 1620-16x20mm	S-SMT FD-F1ag Dip	产品序号	默认-Copper (黄铜)
RN-Rivet Nut (铆螺母)	4-M4 (螺牙)	2-2个					BC-Red Copper (紫铜)
RG-Rivet Gasket (铆垫片)	6-M6 (螺牙)	6-6个					
		8-8个					