




Model No.	POS.1	POS.2	POS.3
1AS1	ON	NONE	ON
Term. Comm.	2-3	N/A	2-1
SCHEMATIC			

SWITCH FUNCTION



SPECIFICATIONS

MECHANICAL LIFE: 30,000 make-and-break cycles.
CONTACT RESISTANCE: 10 mΩ max. initial @ 2-4VDC
 100mA for both silver and gold plated contacts.
INSULATION RESISTANCE: 1,000 MΩ min.
DIELECTRIC STRENGTH: 1,000 Vrms min.@sea level.
OPERATING TEMPERATURE: -40°C to 85°C.

MATERIALS

CASE BUSHING: Glass filled nylon 6/6, flame retardant, heat stabilized(UL94v-0).
ACTUATOR: Brass,chrome plated with internal, O-ring seal standard.
SWITCH SUPPORT: Brass or steel, tin plated.
SWITCH SUPPORT RETAINER: Stainless Steel.
CONTACT/TERMINAL: Copper alloy.
RoHS & Lead Free

	CONTACT PLATING	TERMINAL PLATING	RATINGS
Q	Silver	Gold flash over silver	5 Amps @120 VAC or 28VDC
C	Gold over Silver	Gold over silver	2 Amps @250 VAC
R	Gold	Gold	0.4 Volt-Amps(VA) max. @20V max. (AC or DC)

德利威電子股份有限公司
DAILYWELL ELECTRONICS CO.,LTD.

	符號	原尺寸	修改後尺寸	變更日期	SCALE (比例) : 3 : 2		TITLE 圖 名	Sealed Miniature Toggle Switches			SIZE 圖紙	A4
1	Ⓐ	新增尺寸7.10/操作溫度-30℃修訂為-40℃		APR-12-2019	TOLERANCE (公差) : 0.00mm±0.25mm 0.0mm±0.40mm ANGULAR: ±5° FILE NAME : 1ASP0172		DWG NO. 圖 號	1AS1T2B4M7QES			UNIT 單位	inch mm
2	Ⓑ						REV. 版 本	B	DATE 日期	MAR - 22 - 2006	SHEET 張 數	1 of 1
3	Ⓒ						APPROVE 審 核		CHECK 確 認		DRAW 製 圖	ODA
4	Ⓓ											
5	Ⓔ											