








参考安装方式

NOTES:

备注

- 1.Copper,nickel base,matte tin
黄铜H62, 镍底, 镀雾锡
- 2.Wire screw hole M4
压线螺孔M4
- 3.Current Rating: 60A
额定电流: 60A
- 4.Operating temperature: -40℃ ~ +125℃
工作温度: -40℃ ~ +125℃
- 5.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 6.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * * * - * * * - * * * - 02

Type	Screw Thread	Welding Feet	Series	D-BIP	Product No.	Material
M-Pull Teeth (抽牙)	S-M5 (螺牙)	0808-8x8mm (焊脚)	0808-8x8mm 163D*16x20mm	S-SMT FD-Flag Dip	产品序号	默认=Copper (黄铜) HC=Red Copper (紫铜)
BN-Rivet Nut (铆螺母)	4-M4 (螺牙)	2-2个				
RG-Rivet Gasket (铆垫片)	S-M5 (螺牙)	4-4个				
	6-M6 (螺牙)	6-6个				
		8-8个				

			GENERAL TOLERANCE	制图 DRAWING	02	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK					
			5 or more ±0.35	批准 APPROVAL		产品名称 TITLE	PCB 焊接端子 贴片 抽牙 M4 4焊脚 17.5x10x7.8mm	版本 REV.	A
1	初版发行		2~5 ±0.25	比例 SCALE		产品料号 PART NO.	HC-M44-1710-S071-02	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	0~2 ±0.15	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
			Angle ±3.0°						