





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)





SPECIFICATIONS


Rated Current:1.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Dimension antitheses list					
ITEM	PA	PB	C	W	L
Standard	4.00	1.50	8.0	5.50	12.50
Alternate					



P = With Post



默认 = W/O Post

Ordering Information

PZ	127	-	*	-	N	-	S	-	C*	-	**	-	DP	-	*	-	P
No.of Rows 1=Single Row 2=Dual Row		No.of Pins 2-40Pin		Type Z=直针 W=弯针 S=空板 WS=带贴		(双塑间距)		Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin		Double Plastic (双塑)		Packing R=Reel +Cap (编带+盘)		Post (带柱)			

			GENERAL TOLERANCE		制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK				
			X.X	±0.30	批准 APPROVAL	产品名称 TITLE	1.27双排 双塑 排针 贴片 (编带+盖)	版本 REV.	A
1	初版发行		X.XX	±0.20	比例 SCALE	产品料号 PART NO.	PZ127-2-N-S-C8.0-G0-DP-R	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX	±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
			Angle	±3.0°					