







NOTES:

备注

1. Red Copper, nickel base, matte tin
紫铜T2, 镍底, 镀雾锡
2. Wire screw hole M6
压线螺孔M6
3. Current Rating: 180A
额定电流: 180A
4. Operating temperature: -40°C ~ +125°C
工作温度: -40°C ~ +125°C
5. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
6. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * * * - * * * - * * * - 02

Type	Screw Thread	Welding Feet	Series	D-BIP	Product No.	Material
M-Pull Teeth (抽牙)	S-M6 (螺牙)	S-2个	0808-8x8mm	S-SMT	产品序号	默认=Copper (黄铜)
BN-Rivet Nut (铆螺母)	4-M6 (螺牙)	4-4个	1620-16x20mm	FD-Flag Dip		HC=Red Copper (紫铜)
RG-Rivet Gasket (铆垫片)	S-M6 (螺牙)	6-6个				

			GENERAL TOLERANCE	制图	02	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审核					
			5 or more ±0.35	批准		产品名称	PCB 焊接端子 插板 抽牙 M6	版本	A
			2~5 ±0.25	SCALE		TITLE	8焊脚 16x20x13mm 紫铜	REV.	
1	初版发行		0~2 ±0.15	投影		产品料号	HC-M68-1620-D078RC-02	单位	mm
序号	变更内容	日期	Angle ±3.0°	Projection		PART NO.		页次	1/1
No.	MODIFY CONTENT	MODIFY DATE				MATERIAL		SHEET	