

HC-RBO 12-FE - Covering hood



3247984

<https://www.phoenixcontact.com/us/products/3247984>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Covering hood, depth: 74 mm, width: 49 mm, height: 126 mm, color: black/yellow



Commercial data

Item number	3247984
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	BE19
Product key	BE1Z1X
Catalog page	Page 391 (C-1-2019)
GTIN	4046356724449
Weight per piece (including packing)	41 g
Weight per piece (excluding packing)	38.95 g
Customs tariff number	85389099
Country of origin	IN

HC-RBO 12-FE - Covering hood

3247984

<https://www.phoenixcontact.com/us/products/3247984>



Technical data

Product properties

Product type	Cover profile
--------------	---------------

Dimensions

Width	49 mm
Height	126 mm
Depth	74 mm

Material specifications

Color	multicolored
	black (RAL 9005)
	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

HC-RBO 12-FE - Covering hood

3247984

<https://www.phoenixcontact.com/us/products/3247984>



Classifications

ECLASS

ECLASS-11.0	27141190
ECLASS-12.0	27141190
ECLASS-13.0	27141190

ETIM

ETIM 9.0	EC002848
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-RBO 12-FE - Covering hood



3247984

<https://www.phoenixcontact.com/us/products/3247984>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com