



General ordering data

Order No.	1864050000
Part designation	SL-SMT3.81/2/180G1.5SR
Version	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 2, 180°, Tape
EAN	4032248429172
Qty.	300 pc(s).

System parameters

Fitted to PCB	Reflow solder connection
Outgoing elbow	180°
Pitch	3.81 mm
Pitch in inch	0.15 inch
No. of poles	2
Solder pin length	1.5 mm
Can be coded	Yes
No. of rows	1

System parameters

No. of solder pins per pole	1
Dia. of fitting hole	1.3 mm
Fitting hole tolerance	+ 0.1 mm
L1 in mm	3.81 mm
L1 in inch	0.15 inch
Insulation resistance	1 MΩ
Electric shock protection to DIN VDE 0470	IP 20
Electric shock protection to DIN VDE 0470	Safe from finger touch

Material data

Insulating material	LCP GF
Colour	black
colour chart	Similar to RAL 9011
Insulating material group	IIIa
Flammability class UL 94	V-0
CTI	>= 175
Contact base material	Copper alloy
Contact surface	tinned
Constant operating temp., min.	-25 °C
Constant operating temp., max.	120 °C
Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C
Max. relative humidity during storage	85 %

DIN IEC rating data

Rated current, min. No. pins (Tu=20°C)	16 A
Rated current, min. No. pins (Tu=40°C)	14 A
Rated voltage for overvoltage class/pollution severity III/3	160 V
Rated impulse withstand voltage for overvoltage class/pollution severity III/3	2.5 kV
Rated voltage for overvoltage class/pollution severity III/2	160 V
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	2.5 kV
Rated voltage for overvoltage class/pollution severity II/2	320 V
Rated impulse withstand voltage for overvoltage class/pollution severity II/2	2.5 kV
Short-time withstand current resistance	3 x 1s with 76 A

CSA rating data

Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A

UL 1059 rating data

Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A

Approvals

Approvals institutes



Classifications

ETIM 2.0	NK
ETIM 3.0	EC001284
eClass 4.1	27-26-07-01
eClass 5.0	27-26-07-01
eClass 5.1	27-26-07-04

Similar products

Order No.	Part designation	Version
1863450000	SL-SMT3.81/2/180G3.2SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 2, 180°, Tape
1864060000	SL-SMT3.81/3/180G1.5SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 3, 180°, Tape
1863470000	SL-SMT3.81/3/180G3.2SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 3, 180°, Tape
1864290000	SL-SMT3.81/4/180G1.5SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 4, 180°, Tape
1863490000	SL-SMT3.81/4/180G3.2SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 4, 180°, Tape
1864300000	SL-SMT3.81/5/180G1.5SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 5, 180°, Tape
1863540000	SL-SMT3.81/5/180G3.2SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 5, 180°, Tape
1864310000	SL-SMT3.81/6/180G1.5SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 6, 180°, Tape
1863560000	SL-SMT3.81/6/180G3.2SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 6, 180°, Tape
1864320000	SL-SMT3.81/7/180G1.5SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 7, 180°, Tape
1863570000	SL-SMT3.81/7/180G3.2SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 7, 180°, Tape
1864330000	SL-SMT3.81/8/180G1.5SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 8, 180°, Tape
1863590000	SL-SMT3.81/8/180G3.2SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 8, 180°, Tape

1864340000	SL-SMT3.81/9/180G1.5SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 9, 180°, Tape
1863630000	SL-SMT3.81/9/180G3.2SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 9, 180°, Tape
1864350000	SL-SMT3.81/10/180G1.5SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 10, 180°, Tape
1863660000	SL-SMT3.81/10/180G3.2SR	PCB plug-in connector, Male connectors, Reflow solder connection, Pitch: 3.81 mm, No. of poles: 10, 180°, Tape