



General ordering data

Order No.	1970890000
Part designation	BCF 3.81/18/180F SN OR
Version	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 18, 180°, Box
EAN	4032248680177
Qty.	50 pc(s).

Classifications

eClass 5.1	27-26-07-04
------------	-------------

Similar products

Order No.	Part designation	Version
1970300000	BCF 3.81/02/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1971500000	BCF 3.81/02/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1971070000	BCF 3.81/02/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1970330000	BCF 3.81/03/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1971570000	BCF 3.81/03/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1971100000	BCF 3.81/03/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1970370000	BCF 3.81/04/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1971590000	BCF 3.81/04/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1971130000	BCF 3.81/04/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box

1970380000	BCF 3.81/05/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1971620000	BCF 3.81/05/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1971150000	BCF 3.81/05/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1970400000	BCF 3.81/06/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1971650000	BCF 3.81/06/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1971180000	BCF 3.81/06/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1970440000	BCF 3.81/07/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1971780000	BCF 3.81/07/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1971190000	BCF 3.81/07/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1970550000	BCF 3.81/08/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1971830000	BCF 3.81/08/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1971270000	BCF 3.81/08/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1970570000	BCF 3.81/09/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1971850000	BCF 3.81/09/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1971300000	BCF 3.81/09/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1970580000	BCF 3.81/10/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1971870000	BCF 3.81/10/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1971330000	BCF 3.81/10/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1970620000	BCF 3.81/11/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1971900000	BCF 3.81/11/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1971380000	BCF 3.81/11/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1970650000	BCF 3.81/12/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1971940000	BCF 3.81/12/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1971390000	BCF 3.81/12/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1970690000	BCF 3.81/13/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1971970000	BCF 3.81/13/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box

1971420000	BCF 3.81/13/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1970730000	BCF 3.81/14/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1972000000	BCF 3.81/14/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1971430000	BCF 3.81/14/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1970750000	BCF 3.81/15/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1972030000	BCF 3.81/15/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1971440000	BCF 3.81/15/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1970820000	BCF 3.81/16/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1972070000	BCF 3.81/16/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1971450000	BCF 3.81/16/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1970850000	BCF 3.81/17/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 17, 180°, Box
1972100000	BCF 3.81/17/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 17, 180°, Box
1971460000	BCF 3.81/17/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 17, 180°, Box
1972170000	BCF 3.81/18/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 18, 180°, Box
1971470000	BCF 3.81/18/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 18, 180°, Box
1970900000	BCF 3.81/19/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 19, 180°, Box
1972180000	BCF 3.81/19/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 19, 180°, Box
1971480000	BCF 3.81/19/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 19, 180°, Box
1970950000	BCF 3.81/20/180F SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 20, 180°, Box
1972190000	BCF 3.81/20/180F SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 20, 180°, Box
1971490000	BCF 3.81/20/180F SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 20, 180°, Box