



General ordering data

Order No.	1920720000
Part designation	SAIS 5/9-VA-B-COD
Version	Sensor/Actuator plug-in connector, M12, pin, straight, Tension clamp connection
EAN	4032248561445
Qty.	1 pc(s).

Technical data

Ambient temperature, max.	85 °C
Ambient temperature, min.	-40 °C
Bus line connection via	Tension clamp connection
Cable connection diameter	6...8 mm
Cable diameter, max.	8 mm
Cable diameter, min.	6 mm
Cable gland	PG 9
Connection cross-section	0.25...0.5 mm ²
Connection cross-section, max.	0.5 mm ²
Connection cross-section, min.	0.25 mm ²
Contact surface	CuSnZn
Contact tube diameter	M12
Housing material	14V32
Ordering data, title	5-pole, straight
Protection class	IP 69 k
Rated current	4 A
Rated voltage	125 V
No. of poles	5
Version	pin, straight

Classifications

ETIM 2.0	EC000516
ETIM 3.0	EC002062
eClass 4.1	27-26-07-01
eClass 5.0	27-26-07-01
eClass 5.1	27-26-07-01

Classifications

Similar products

Order No.	Part designation	Version
1920700000	SAIS 5/9-VA	Sensor/Actuator plug-in connector, M12, pin, straight, Tension clamp connection