




序号/Rev.No.	名称/Title	文件编号/File No.
1	XY636螺丝	
2	XY636方针	
3	XY636端子	
4	XY636-7.62塑件	



Poles: 2P&3P-24P
Pitch: 7.62mm
Voltage Rating: 300V
Current Rating: 30A
Wire range: 26-10AWG 4.0mm²
Housing: PA66(UL 94V-0)
Wire Cage: Brassl, Nickel Plated
Solder Pin: Brass, Tin Plated
Screw: M3.0, Steel, Zinc Plated
Torque: 0.5N.m