

修 订 REV NO	标 记 MARK	修 改 描 要 REVISION DESCRIPTION	签 名 SIGNATURE	日 期 DATE
		NEW DWG		2016-03-12

SPECIFICATIONS

Current Rating: 2Amps  
 Insulator Resistance: 5000Megohms min.  
 Dielectric Withstanding: AC 500v  
 Operating Temperature: -40°~ +105°c  
 Contact Material: Brass  
 Insulator Material: PA6T  
 PLTAING: GOLD FLASH





UNSPECIFIED TOLERANCE: ±0.20

Dimensions List

Contacts Per row	Dimensions		Contacts Per row	Dimensions	
	A	B		A	B
1	1.27	0	1*21	26.67	25.40
1*2	2.54	1.27	1*22	27.94	26.67
1*3	3.81	2.54	1*23	29.21	27.94
1*4	5.08	3.81	1*24	30.48	29.21
1*5	6.35	5.08	1*25	31.75	30.48
1*6	7.62	6.35	1*26	33.02	31.75
1*7	8.89	7.62	1*27	34.29	33.02
1*8	10.16	8.89	1*28	35.56	34.29
1*9	11.43	10.16	1*29	36.83	35.56
1*10	12.70	11.43	1*30	38.10	36.83
1*11	13.97	12.70	1*31	39.37	38.10
1*12	15.24	13.97	1*32	40.64	39.37
1*13	16.51	15.24	1*33	41.91	40.64
1*14	17.78	16.51	1*34	43.18	41.91
1*15	19.05	17.78	1*35	44.45	43.18
1*16	20.32	19.05	1*36	45.72	44.45
1*17	21.59	20.32	1*37	46.99	45.72
1*18	22.86	21.59	1*38	48.26	46.99
1*19	24.13	22.86	1*39	49.53	48.26
1*20	25.40	24.13	1*40	50.80	49.53

Plastic Base

Type	
H	1.0
PA	4.0
PB	3.0
PC	2.4



PCB LAYOUT

深圳市华德共创科技有限公司  
 Shenzhen Huade co-create Technology Co.,LTD  
 电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			TITLE: 产品名称: 1.27*1.0 弯针PA4.0 PB3.0 PC2.5			
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC127-PW1-n			
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001