



RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)



深圳市韩下电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ± 0.30 X° : $\pm 5^\circ$

X.X : ± 0.25 X.X° : $\pm 1^\circ$

X.XX : ± 0.20 X.XX° : $\pm 0.5^\circ$

DRAWN NAME HX PM1.27-1x5P ZC H4.6

SIZE A4 SCALE N:1 PROUT NO.

REV A UNIT mm PROJECT PAGE 1/1

DRAW: 黄彬 2022/06/07 CHECKED: 张伟 2022/06/07 APPROVED: 罗小春 2022/06/07

| No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 1 | — | — | 11 | 12.70 | 13.97 | 21 | 25.40 | 26.67 | 31 | 38.10 | 39.37 | 41 | 50.80 | 52.07 |
| 2 | 1.27 | 2.54 | 12 | 13.97 | 15.24 | 22 | 26.67 | 27.94 | 32 | 39.37 | 40.64 | 42 | 52.07 | 53.34 |
| 3 | 2.54 | 3.81 | 13 | 15.24 | 16.51 | 23 | 27.94 | 29.21 | 33 | 40.64 | 41.91 | 43 | 53.34 | 54.61 |
| 4 | 3.81 | 5.08 | 14 | 16.51 | 17.78 | 24 | 29.21 | 30.48 | 34 | 41.91 | 43.18 | 44 | 54.61 | 55.88 |
| 5 | 5.08 | 6.35 | 15 | 17.78 | 19.05 | 25 | 30.48 | 31.75 | 35 | 43.18 | 44.45 | 45 | 55.88 | 57.15 |
| 6 | 6.35 | 7.62 | 16 | 19.05 | 20.32 | 26 | 31.75 | 33.02 | 36 | 44.45 | 45.72 | 46 | 57.15 | 58.42 |
| 7 | 7.62 | 8.89 | 17 | 20.32 | 21.59 | 27 | 33.02 | 34.29 | 37 | 45.72 | 46.99 | 47 | 58.42 | 59.69 |
| 8 | 8.89 | 10.16 | 18 | 21.59 | 22.86 | 28 | 34.29 | 35.56 | 38 | 46.99 | 48.26 | 48 | 59.69 | 60.96 |
| 9 | 10.16 | 11.43 | 19 | 22.86 | 24.13 | 29 | 35.56 | 36.83 | 39 | 48.26 | 49.53 | 49 | 60.96 | 62.23 |
| 10 | 11.43 | 12.70 | 20 | 24.13 | 25.40 | 30 | 36.83 | 38.10 | 40 | 49.53 | 50.80 | 50 | 62.23 | 63.50 |