




RoHS

REV.	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2025.02.19

- 技术要求:
- 1.打铜底0.5-1μm,镍2-2.5μm, 镀雾锡3-5μm。
 - 2.铆好后不得有松动现象。
 - 3.插脚尖部符合可焊性要求。
 - 4.螺纹需符合通止规/止针要求。
 - 5.螺纹扭矩: 2.5Nm.
 - 6.额定电流: 150A.

>30.±0.4	X.°±	PART NO: TTR64170200-1500		XFCN 兴飞连接器	
6-30±0.3	.X°±	TITLE: PCB SOLDERING TERMINAL		0769-82001899	
0-6±0.2	.XX°±			www.xfconn.com	
ANGLES±1°	.XXX°±			DWG NO: /	
UNITS:	mm	APPD	Chen ZhiQiang		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		CHKD	Liu Wei	VIEW	
		DRAW	Chen HongJiang	SCALE	SHEET REV
		DATE	2025.02.19	NONE	1/1 A1

2	垫片		SPCC	1
1	插脚		T2 (Y2)	1
序号	名称	零件编号	材质	数量