






RoHS



- 技术要求:
- 1.打铜底0.5-1 μ m,镍2-2.5 μ m, 镀雾锡3-5 μ m。
 - 2.铆好后不得有松动现象。
 - 3.插脚尖部符合可焊性要求。
 - 4.螺纹需符合通止规/止针要求。
 - 5.螺纹扭矩: 2.5Nm.
 - 6.额定电流 : 180A.



2	垫片		SPCC	1
1	插脚		H62 (Y2)	1
序号	名称	零件编号	材质	数量

>30.±0.4	X.°±
6-30±0.3	.X°±
0-6±0.2	.XX°±
ANGLES±1°	.XXX°±
UNITS:	mm
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN	

PART NO:		TT68160200-1300		XFCN 兴飞连接器		
TITLE: PCB SOLDERING TERMINAL		0769-82001899				
		www.xfconn.com				
		DWG NO:		/		
APPD		Chen ZhiQiang				
CHKD		Liu Wei		VIEW		
DRAW		Chen HongJiang		SCALE	SHEET	REV
DATE		2025.02.19		NONE	1/1	A1