



PCB LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ MAX

接触电阻: ≤20mΩ MAX

X2001 H I -2xXX - PT AuN
① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:H- HSG
- 3.Welding Board Angle:I-HSG+hardware
- 4.Row No-Pin No:2xXX-2x03P~2x25P
- 5.Material:PT-PBT UL94V-0
- 6.Plating:AuN-Terminal half- Gold nickel

NUMBER OF POSITIONS	DIMENSION		NUMBER OF POSITIONS	DIMENSION	
	A	B		A	B
2x03	10.20	4.00	2x13	30.20	24.00
2x04	12.20	6.00	2x14	32.20	26.00
2x05	14.20	8.00	2x15	34.20	28.00
2x06	16.20	10.00	2x16	36.20	30.00
2x07	18.20	12.00	2x17	38.20	32.00
2x08	20.20	14.00	2x18	40.20	34.00
2x09	22.20	16.00	2x20	44.20	38.00
2x10	24.20	18.00	2x22	48.20	42.00
2x11	26.20	20.00	2x25	48.20	48.00
2x12	28.20	22.00	/		

X2001HI-2xXX-PTAuN	PBT	Brass	XPD1.0-A28PXX-IDC	X2001HA-2xXX X2001HA2-2xXX X2001HA3-2xXX
PART NO	Material	Material(pin)	Suitable XKB flat cable	Suitable XKB IDC

							DSND		SCALE: N/A	MODEL TYPE: 2.00mm DIP			
					ANGLAR	±5°		DWN		VIEW: 	PART NO.: X2001HI-2xXX-PTAuN		
Δx					L ≤ 4	±0.2		CHKD		UNIT: mm/in	DWG NO.: X-X2001HI-2xXX-PTAuN		
Δx					4<L ≤ 16	±0.3		APPD		SIZE: A4			
Δx					16<L ≤ 63	±0.4							
Δx					L > 63	±0.5							
MARK	DESCRIPTION				DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED		
REVISIONS										WEIGHT	SHEET	REVISION	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn											1/1	A0	