





RoHS

REV	ECN NO.	DESRPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2025.02.19

- 技术要求:
- 1.打铜底0.5-1μm,镍2-2.5μm，镀哑锡3-5μm。
 - 2.铆好后不得有松动现象。
 - 3.插脚尖部符合可焊性要求。
 - 4.螺纹需符合通止规/止针要求。
 - 5.额定电流：80A.

>30.±0.4	X.°±	PART NO: T4288100-2000		XFCN 兴飞连接器						
6-30±0.3	.X°±									
0-6±0.2	.XX°±	TITLE: PCB SOLDERING TERMINAL		0769-82001899						
ANGLES±1°	.XXX°±			www.xfconn.com						
UNITS:	mm	APPD Chen ZhiQiang		DWG NO: /						
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN										
							CHKD Liu Wei		VIEW 	
							DRAW Chen HongJiang		SCALE SHEET	
		DATE 2025.02.19		NONE 1/1		A1				

1	插脚		H62 (Y2)	1
序号	名称	零件编号	材质	数量