

NOTES

MATERIAL

- 1.HOUSING MATERIAL: LCP BLACK UL94V-0.
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE .
- 3.PLATING: GOLD FLASH PLATING OVER NICKEL.
- 4.SHIELD: COPPER ALLOY WITH NICKEL PLATED.

5.LED: TIN PLATED.

ELECTRICAL






- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING 1.5 AMP.
- 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
- 5.DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL

- 1.DURRABILITY: 750 CYCLES MIN.
- 2.MATING/UNMATING FORCE: 2.24 KG.F MAX.

ENVIRONMENTAL:

- 1.STORAGE: -40℃~+85℃.
- 2.OPERATION: -40℃~+85℃.

PCBLAYOUT
TOL:±0.05

PART NUMBER DESCRIPTION:

RJ45-005-0XX-XX

电镀码

1-GOLD FLASH

3-3u''Au

流水码



1:LCP黑 盘装

2:LCP黑 卷装

类别码

31:正向 4.1有壳 左黄右绿

32:正向 4.1有壳 左绿右黄



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES		 	TITLE: RJ45 9.9H 沉板5.8 DIP 带灯		
			PAR	RJ45-005-031-11	
DECIMALS:	ANGLES:		DWN		
.X:±0.35	X'':±3'		CHKD		
.XX:±0.25	.X'':±2"		APVD		
.XXX:±0.15	.XX'':±1*	SCALE1:1	UNIT:MM		
		CUSTOMER COPY	SIZE:A4	SHEET:1F1	REV:A