








PART NUMBER DESCRIPTION:

RJ45-001-012-XX

电镀码

1-DOLD FLASH

流水码

1:LCP黑 盘装

2:LCP黑 卷装

NOTES:

1. HOUSING MATERIAL:GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL:COPPER ALLOY,T=0.30.
3. PLATING: GOLD PLATED ON CONTACT AREA, 100u"MIN. TIN PLATED ON SOLDERING AREA, 50u"MIN. NICKEL PLATED OVERALL.
4. SHELL:COPPER ALLOY,T=0.20. 40u"MIN. NICKEL PLATED OVERALL.

ELECTRICAL:


1. VOLTAGE RATING: 125V AC RMS.
 2. CURRENT RATING: 1.5AMP.
 3. CONTACT RESISTANCE: 40MILLIOHMS MAX.
 4. INSULATION RESISTANCE: 500MEGOHMS MIN @100V DC.
- MECHANICAL:
1. DURRABILITY: 750 CYCLES MIN.
 - 2.INSERTION FORCE : 22N MAX.
 - 3.REMOVAL FORCE(WITHOUT PLUG LOCK) : 22N MAX.

ENVIRONMENTAL:

1. STORAGE: -40°C~85°C
2. OPERATION: -40°C~85°C

*Apply to the EU standards(ROSH)

1. (01)~(06) FOR QIP DIM.

PCBLAYOUT TOP VIEW
TOL:±0.05(THICKNESS=1.60)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			
DECIMALS:	ANGLES:	TITLE: RJ45 讯普2.8 有壳 DIP	
.X:±0.35	X":±3'	PAR	RJ45-001-012-11
.XX:±0.25	.X":±2'	DWN	
.XXX:±0.15	.XX":±1'	CHKD	
		APVD	
		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
		CUSTOMER COPY	REV:A