







NOTES

MATERIAL

- 1.HOUSING MATERIAL:THERMO PLASTICS UL94V-0 .
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE T=0.25mm.
SELECT GOLD PLATING ON CONTACT AREA AND TIN
PLATING ON SOLDER AREA OVER NICKEL.
- 3.SHIELD: STAINLESS T=0.20mm NI PLATING.
- 4.GASKET :SPCC T=0.40 NI PLATING.
- 5.LED:TIN PLATING.

MELECTRICAL




- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING: 1.5 AMP.
- 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
- 5.DIELECTRIC DIELECTRIC
RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL

- 1.DURRABILITY: 750 CYCLES MIN.
- 2.MATING/UNMATING FORCE: 2.24 KG.F MAX.

ENVIRONMENTAL:

- 1.STORAGE: -40℃~+85℃.
- 2.OPERATION: -40℃~+85℃.



PART NUMBER DESCRIPTION:

RJ45-005-201-XX

电镀码

1-GOLD FLASH



3-3u''Au

流水码

1:LCP黑 盘装

2:LCP黑 卷装


3:LCP本 盘装



8	—
7	—
6	RX—
5	—
4	—
3	RX+
2	TX—
1	TX+
PIN	说明

LED electrical characteristic

Node		
A1(+)	A2(-)	A1—A2
B1(+)	B2(-)	B1—B2



PCBLAYOUT T=1.2

TOL:±0.05

MANUFACTURE DWG

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

.X:±0.35

.XX:±0.25

.XXX:±0.15

ANGLES:

X':±3'

.X':±2'

.XX':±1'

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,Ltd

TITLE:

RJ45 沉板4.0 DIP 带壳 无灯

PAR RJ-005-201-11

DWN

CHKD

APVD

SCALE1:1 UNIT:MM

SIZE:A4 SHEET:1F1

REV:A

CUSTOMER COPY