







NOTES

MATERIAL

- 1.HOUSING MATERIAL: THERMO PLASTICS UL94V-0.
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
- 3.PLATING: GOLD PLATING OVER NICKEL.

ELECTRICAL

- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING: 1.5 AMP.
- 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
- 5.DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL

- 1.DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:

- 1.OPERATION: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.STORAGE: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.

PART NUMBER DESCRIPTION:

RJ45-542-020-XX

流水码


1:PBT黑盘装

2:PA46黑盘装

3:PBT黄0405

电镀码

1-GOLD FLASH

PCB LAYOUT T=1.6
TOP VIEW TOL:±0.05

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			
DECIMALS:	ANGLES:	TITLE: 5301 1x4 全塑 DIP B款	
.X:±0.35	X':±3'	PAR	RJ45-542-020-31
.XX:±0.25	.X':±2'	DWN	
.XXX:±0.15	.XX':±1'	CHKD	
		APVD	
		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
		CUSTOMER COPY	REV:A