

NOTES

MATERIAL

- 1.HOUSING MATERIAL: LCP BLACK UL94V-0.
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE $T=0.25mm$.
- 3.PLATING: GOLD AND TIN PLATING OVER NICKEL.
- 4.SHIELD: BRASS WITH NICKEL PLATED.

ELECTRICAL



- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING: 1.5 AMP.
- 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC.
- 5.DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL


- 1.DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:

- 1.STORAGE: $-40^{\circ}C \sim +85^{\circ}C$.
- 2.OPERATION: $-40^{\circ}C \sim +85^{\circ}C$.



8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN	说明



PCBLAOUT T=1.2

TOL:±0.05

PART NUMBER DESCRIPTION:

RJ45-104-001-XX

电镀码


1-GOLD FLASH

3-3u''Au

流水码

1:LCP黑 盘装

2:LCP黑 卷装



壳子脚

焊脚尺寸以顺畅过孔规为准

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: RJ45 9.9H 流板5.8 有壳无灯DIP	
			PAR	RJ45-104-001-11
DWN				
CHKD				
APVD				
SCALE1:1				
DECIMALS:	ANGLES:	UNIT:MM		
.X:±0.35	.X':±3"	CUSTOMER COPY	SIZE:A4	SHEET:1F1
.XX:±0.25	.X':±2"			REV:A
.XXX:±0.15	.XX':±1"			