

NOTES:

1. HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL: COPPER ALLOY, T=0.35.
3. PLATING: GOLD PLATED ON CONTACT AREA, 100u"MIN. MATTE TIN PLATED ON SOLDERING AREA, 50u"MIN. NICKEL PLATED OVERALL.
4. SHELL: COPPER ALLOY, T=0.20. 40u"MIN. NICKEL PLATED OVERALL.
5. LED: T=0.50, MATE TIN PLATED.

ELECTRICAL:

1. VOLTAGE RATING: 125V AC RMS.
2. CURRENT RATING: 1.5AMP.
3. CONTACT RESISTANCE: 40MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500MEG OHMS MIN @100V DC.







MECHANICAL:

1. DURABILITY: 750 CYCLES MIN.
2. INSERTION FORCE: 22N MAX.
3. REMOVAL FORCE (WITHOUT PLUG LOCK): 22N MAX.

ENVIRONMENTAL:

1. STORAGE: -40°C~85°C
2. OPERATION: -40°C~85°C

*Apply to the EU standards (ROSH)



PART NUMBER DESCRIPTION:

RJ45-003-0XX-XX

电镀码

1-GOLD FLASH

3-3u" Au

5-5u" AU

7-15u" AU

8-30u" AU

流水码

1: LCP 黑 盘装



2: LCP 黑 卷装

类别码

13: 3.0脚 带弹 左黄右绿

14: 3.0脚 带弹 左绿右黄

8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN	说明



PCBLAYOUT

TOL: ±0.05

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: RJ45 沉板3.0 带弹 带灯	
DECIMALS:	ANGLES:	PAR	RJ45-003-014-11
.X: ±0.35	X°: ±3'	DWN	
.XX: ±0.25	.X°: ±2'	CHKD	
.XXX: ±0.15	.XX°: ±1'	APVD	
CUSTOMER COPY		SCALE 1:1	UNIT: MM
		SIZE: A4	SHEET: 1F1
			REV: A