


NOTES:

1. Rated voltage: 250V AC.DC
2. Rated current: 7A AC DC
3. Contact resistance: $\leq 20 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
5. Withstand voltage: 1500V AC/minute
6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
7. Material : Nylon UL94V-0(2)
8. Pin Materials : Brass/Tin-Plated.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL39605(CT3.96B)-11AW		TITLE: 3.96 mm Pitch Wire To Board Wafer	
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE:21/08/22	PART NO:	
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE:21/08/22	SCALE: N/A	PAGE: 1/1
FINISH:		APPD:Ren An De	DATE:21/08/22	UNITS: mm	REV.: A
DRAWING NO:					