








REV.	REVISION DESCRIPTION	DATE	APPD


NOTES:

- 1. Rated voltage: 250V AC.DC
- 2. Rated current: 3A AC DC
- 3. Contact resistance: $\leq 20\text{ m}\Omega$
- 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
- 5. Withstand voltage: 1000V AC/minute
- 6. Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
- 7. Material : Nylon UL94V-0(2)
- 8. Pin Materials : Brass/Tin-Plated.



Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2	2510B-2AW	2.5	5.0	10	2510B-10AW	22.5	25.0
3	2510B-3AW	5.0	7.5	11	2510B-11AW	25.0	27.5
4	2510B-4AW	7.5	10.0	12	2510B-12AW	27.5	30.0
5	2510B-5AW	10.0	12.5	13	2510B-13AW	30.0	32.5
6	2510B-6AW	12.5	15.0	14	2510B-14AW	32.5	35.0
7	2510B-7AW	15.0	17.5	15	2510B-15AW	35.0	37.5
8	2510B-8AW	17.5	20.0	-	-	-	-
9	2510B-9AW	20.0	22.5	-	-	-	-

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL25016 (2510B)-AW		TITLE: 2.50 mm Pitch Wire To Board Wafer	
.XX: ± 0.15	.X° : ± 2.0°				
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Chen Quan Long	DATE:21/08/01	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE:21/08/01		
DRAWING NO:		APPD:Ren An De	DATE:21/08/01	SCALE: N/A	PAGE: 1/1
				UNITS: mm	REV. : A




REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
1. Rated voltage: 250V AC. DC
 2. Rated current: 3A AC DC
 3. Contact resistance: $\leq 20\text{ m}\Omega$
 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 5. Withstand voltage: 1000V AC/minute
 6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 7. Material : Nylon UL94V-0(2)
 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL25016 (2510B)-Y		TITLE: 2.50 mm Pitch Wire To Board Wafer	
.XX: ± 0.15	.X° : ± 2.0°				
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Chen Quan Long	DATE:21/08/01	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE:21/08/01		
DRAWING NO:		APPD:Ren An De	DATE:21/08/01	UNITS: mm	REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD



NOTES:

Rated voltage: 250V AC.DC

Rated current: 3A AC DC

Contact resistance: $\leq 20\text{ m}\Omega$

Insulation resistance: $\geq 1000\text{ M}\Omega$

Withstand voltage: 1000V AC/minute

Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$

Wire range: AWG#28~#22

Materials:

Terminal: Phosphor bronze, Tin plated

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL25016 (2510B)-T	TITLE: 2.5 mm Pitch Crimp Terminal
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 20.11.27
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 20.11.27
FINISH:		APPD: Ren An De	DATE: 20.11.27
DRAWING NO:		UNITS: mm	REV.: A