




REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			

四代端子

- NOTES:
- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - INSULATION RESISTANCE: 5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
 - MATERIAL:
 - SEE TABLE
 - ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管，OD:2.0MM	AS
③	端子	国产I-PEX 四代端子，镀金	1
②	接头	SMA母头母针,4脚半牙(牙长5mm),带凹槽,镀金,外螺纹内孔	1
①	同轴线	RF0.81cable同轴线，OD:0.8mm	AS

深圳市金航标电子有限公司

ALL DIMENSION ARE IN MM	DRAWN	Jamy	DATE	2022-12-12	KH-IPEX4-SMAKWE5-RG0.81-B0300H		
	ENG.						
	COMPUTER GENERATED IN SOLIDWORKS	MFG.					
	DO NOT SCALE THIS DRAWING	Q.A.					
PROJECTION		GENERAL TOLERANCE FOR ANGLES			SIZE	Number	REV
		X.X X.XX X.XXX			B		A
		± 1° ± 0.3 ± 0.25 ± 0.150			SCALE: Free		
					TYPE		
					SHEET 1 OF 1		

CUSTOMER P/N: