




REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			

NOTES:

1. ELECTRICAL:

- 1.1. VOLTAGE RATING:DCV 300V 10MS
1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.

2. MATERIAL:

- 2.1. SEE TABLE

3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管，OD:2.0MM	AS
③	端子	国产I-PEX 一代端子，镀金	1
②	接头	SMA母头母针,4脚半牙(牙长5mm),不带凹槽,镀金,外螺纹内孔	1
①	同轴线	RF1.37cable, 黑色同轴线，OD:1.37mm	AS

深圳市金航标电子有限公司

ALL DIMENSION ARE IN MM	DRAWN Jamy	DATE 2022-12-12	KH-IPEX-SMAKWE5-RG1.37-B140H		
	ENG.				
	MFG.				
COMPUTER GENERATED IN SOLIDWORKS	MFG.		SIZE Number		
DO NOT SCALE THIS DRAWING	Q.A.				
PROJECTION	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150		B		REV A
CUSTOMER P/N:		SCALE: Free		TYPE	SHEET 1 OF 1