




| REVISIONS |        |             |     |     |      |
|-----------|--------|-------------|-----|-----|------|
| REV       | NUMBER | DESCRIPTION | DWN | CHK | DATE |
| A         |        | DESIGN      |     |     |      |
|           |        |             |     |     |      |

NOTES:

1. ELECTRICAL:

- 1.1. VOLTAGE RATING:DCV 300V 10MS  
1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.  
1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.  
1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST  
1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.

2. MATERIAL:

- 2.1. SEE TABLE

3. ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION                       | QTY. |
|----------|-------------|-----------------------------------|------|
| ④        | 套管          | 黑色热缩套管，OD:2.0MM                   | AS   |
| ③        | 端子          | 国产I-PEX 一代端子，镀金                   | 1    |
| ②        | 接头          | SMA母头母针,4脚半牙(牙长5mm),不带凹槽,镀金,外螺纹内孔 | 1    |
| ①        | 同轴线         | RF1.78cable, 黑色同轴线，OD:1.78mm      | AS   |

深圳市金航标电子有限公司

|                                  |                                                                       |                 |                               |        |       |
|----------------------------------|-----------------------------------------------------------------------|-----------------|-------------------------------|--------|-------|
| ALL DIMENSION ARE IN MM          | DRAWN Jamy                                                            | DATE 2022-12-12 | KH-IPEX-SMAKWE5-RG1.78-B50H   |        |       |
|                                  | ENG.                                                                  |                 |                               |        |       |
|                                  | MFG.                                                                  |                 |                               |        |       |
| COMPUTER GENERATED IN SOLIDWORKS | Q.A.                                                                  |                 |                               |        |       |
| DO NOT SCALE THIS DRAWING        |                                                                       |                 | SIZE B                        | Number | REV A |
| PROJECTION                       | GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150 |                 | SCALE: Free TYPE SHEET 1 OF 1 |        |       |

CUSTOMER P/N: