


REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



四代端子

NOTES:

1. ELECTRICAL:

- | | | |
|------|--|--|
| 1.1. | VOLTAGE RATING:DCV 300V 10MS | |
| 1.2. | CONDUCTANCE RESISTANCE: 3.0 OHM/MAX. | |
| 1.3. | INSULATION RESISTANCE: 5.0M OHM/MIN. | |
| 1.4. | THE CABLE SHOULD BE 100% ELECTRICAL TEST | |
| 1.5. | IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES. | |

2. MATERIAL:

- 2.1. SEE TABLE

3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	端子	国产I-PEX 四代端子, 镀金	1
②	接头	SMA母头母针,4脚半牙(牙长5mm),带凹槽,镀金,外螺纹内孔	1
①	同轴线	RF0.81cable同轴线, OD:0.8mm	AS

深圳市金航标电子有限公司

ALL DIMENSION ARE IN MM	DRAWN Jamy	DATE 2022-12-12	KH-IPEX4-SMAKWE5-RG0.81-B060H			
	ENG.					
	MFG.					
	Q.A.					
COMPUTER GENERATED IN SOLIDWORKS			SIZE	Number		REV
DO NOT SCALE THIS DRAWING			B			A
PROJECTION	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150		SCALE: Free		TYPE	SHEET 1 OF 1
