


REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



四代端子

NOTES:

1. ELECTRICAL:

1.1. VOLTAGE RATING:DCV 300V 10MS

1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.

1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.

1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST

1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.


2. MATERIAL:

2.1. SEE TABLE

3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	端子	国产I-PEX 四代端子, 镀金	1
②	接头	SMA母头母针,4脚半牙(牙长5mm),带凹槽,镀金,外螺纹内孔	1
①	同轴线	RF0.81cable同轴线, OD:0.8mm	AS

深圳市金航标电子有限公司

ALL DIMENSION ARE IN MM	DRAWN Jamy	DATE 2022-12-12	KH-IPEX4-SMAKWE5-RG0.81-B0140H		
	ENG.				
	MFG.				
	Q.A.				
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING			SIZE B	Number	REV A
PROJECTION 	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150		SCALE: Free TYPE SHEET 1 OF 1		