




SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance:1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature:-40° to+105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240° C for30-60seconds
(260° C for5seconds)

RECOMMEND P. C. B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

 深圳市韩下电子有限公司					No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
					1	0.00	2.54	11	25.40	27.94	21	50.80	53.34	31	76.20	78.74
					2	2.54	5.08	12	27.94	30.48	22	53.34	55.88	32	78.74	81.28
					3	5.08	7.62	13	30.48	33.02	23	55.88	58.42	33	81.28	83.82
					4	7.62	10.16	14	33.02	35.56	24	58.42	60.96	34	83.82	86.36
					5	10.16	12.70	15	35.56	38.10	25	60.96	63.50	35	86.36	88.90
					6	12.70	15.24	16	38.10	40.64	26	63.50	66.04	36	88.90	91.44
					7	15.24	17.78	17	40.64	43.18	27	66.04	68.58	37	91.44	93.98
					8	17.78	20.32	18	43.18	45.72	28	68.58	71.12	38	93.98	96.52
					9	20.32	22.86	19	45.72	48.26	29	71.12	73.66	39	96.52	99.06
					10	22.86	25.40	20	48.26	50.80	30	73.66	76.20	40	99.06	101.60


UNLESS OTHEWIXE SPECIFIED TOLERANCE

X : ±0.30 X° : ±5°
X.X : ±0.25 X.X° : ±1°
X.XX : ±0.20 X.XX° : ±0.5°

DRAWN NAME:

HX PM2.54-1x4P WT

SIZE	A4	SCALE	N:1	PROUCT NO.
REV	A	UNIT	mm	PROJECT

 PAGE 1/1

DRAW: 黄彬 2024/08/13

CHECKED: 张伟 2024/08/13

APPROVED: 罗小春 2024/08/13