





ROHS



12.95 [0.510]



3D View



Specifications(规格):


- 1.Impedance(特性阻抗): 50Ω;
- 2.Frequency (工作频率): DC~6GHz;
- 3.VSWR (电压驻波比): 1.50 @3GHz;  
1.60 @6GHz;
- 4.Insulation resistance(绝缘阻抗): ≥100MΩ;
- 5.Dielectric withstand voltage (介质耐电压): 800V AC;
- 6.Mating cycles (耐久性): ≥25;
- 7.Engagement force(啮合力): ≤25N;
- 8.Retention force latch(保持力): ≥110N;
- 9.Temperature range(使用温度): -40℃~+105℃;

PART NO.:

XK1PLF1S7-NA26-X

Code: A~Z

BOM List:



|     |                  |              |                  |       |           |
|-----|------------------|--------------|------------------|-------|-----------|
| 7   | Outer Ferrule    | Copper Alloy | Ni PLATED        | 1 PC  |           |
| 6   | Spring           | Copper Alloy | Tin PLATED       | 1 PC  |           |
| 5   | Dielectric       | PP           |                  | 1 PC  |           |
| 4   | Outer Conductor  | Zinc Alloy   | Tin PLATED       | 1 PC  |           |
| 3   | Center Conductor | Copper Alloy | Gold PLATED      | 1 PC  | 5000PCS/R |
| 2   | Housing          | PBT          |                  | 1 PC  |           |
| 1   | Secondary Lock   | PBT          |                  | 1 PC  |           |
| NO. | SPEC.            | MATERIAL     | FINISH (Contact) | Q' TY | Note      |

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn



XKB INDUSTRIAL PRECISION CO.,LIMITED

|          |    |             |
|----------|----|-------------|
| DESIGN   | 希文 | VIEW:       |
| CHECKED  |    | UNIT: mm/in |
| APPROVED |    | SIZE: A4    |

|                        |       |
|------------------------|-------|
| ANGLAR                 | ±5°   |
| X.                     | ±0.50 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.10 |
| UNSPECIFIED TOLERANCES |       |

|                                               |  |  |
|-----------------------------------------------|--|--|
| MODEL TYPE:<br>FAKRA Female Connector for 302 |  |  |
| PART NO.:<br>XK1PLF1S7-NA26-X                 |  |  |
| DWG NO.:<br>X-XK1PLF1S7-NA26-X                |  |  |

|       |      |          |
|-------|------|----------|
| SCALE | PAGE | REVISION |
| N/A   | 1/2  | A0       |

1















2

3

4

| REVISIONS |         |          |                 |            |
|-----------|---------|----------|-----------------|------------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       |
| A0        | N/A     |          | INITIAL RELEASE | 2024.08.22 |
|           |         |          |                 |            |

Code List:

|               |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |                                                                                     |                                                                                     |
|---------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| Colde         |  |  |  |  |  |  |  |
|               | A                                                                                 | B                                                                                 | C                                                                                  | D                                                                                   | E                                                                                   | F                                                                                   | G                                                                                   |
| Color/RAL-No. | Black/9005                                                                        | White/9001                                                                        | Blue/5005                                                                          | Bordeaux/4004                                                                       | Green/6002                                                                          | Brown/8011                                                                          | Grey/7031                                                                           |
| PART NO.      | XK1PLF1S7-NA26-A                                                                  | XK1PLF1S7-NA26-B                                                                  | XK1PLF1S7-NA26-C                                                                   | XK1PLF1S7-NA26-D                                                                    | XK1PLF1S7-NA26-E                                                                    | XK1PLF1S7-NA26-F                                                                    | XK1PLF1S7-NA26-G                                                                    |
| Colde         |  |  |  |  |  |  |  |
|               | H                                                                                 | I                                                                                 | K                                                                                  | L                                                                                   | M                                                                                   | N                                                                                   | Z                                                                                   |
| Color/RAL-No. | Violet/4003                                                                       | Beige/1001                                                                        | Curry/1027                                                                         | Carmine red/3002                                                                    | Pastel Orange/2003                                                                  | Pastel Green/6019                                                                   | Water Blue/5021                                                                     |
| PART NO.      | XK1PLF1S7-NA26-H                                                                  | XK1PLF1S7-NA26-I                                                                  | XK1PLF1S7-NA26-K                                                                   | XK1PLF1S7-NA26-L                                                                    | XK1PLF1S7-NA26-M                                                                    | XK1PLF1S7-NA26-N                                                                    | XK1PLF1S7-NA26-Z                                                                    |

|                        |       |
|------------------------|-------|
| ANGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|          |    |                                                                                             |                                               |
|----------|----|---------------------------------------------------------------------------------------------|-----------------------------------------------|
| DESIGN   | 希文 | VIEW:  | MODEL TYPE:<br>FAKRA Female Connector for 302 |
| CHECKED  |    | UNIT: mm/in                                                                                 | PART NO.:<br>XK1PLF1S7-NA26-X                 |
| APPROVED |    | SIZE: A4                                                                                    | DWG NO.:<br>X-XK1PLF1S7-NA26-X                |
|          |    |                                                                                             | SCALE: N/A                                    |
|          |    |                                                                                             | PAGE: 2/2                                     |
|          |    |                                                                                             | REVISION: A0                                  |

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

1

2

3

4